

Unattended Measurement System (UMS)

International Partnership for Nuclear Disarmament Verification (IPNDV) Working Group 3

Geneva, Switzerland

18-19 February, 2016

Hirofumi TOMIKAWA, Yoshiki KIMURA

Integrated Support Center for Nuclear Nonproliferation and Nuclear Security

Japan Atomic Energy Agency

(IAEA) Overview of Unattended NDA system

UMS might be applicable to chain of custody, NM detection (quantification), storage monitoring without leakage of sensitive information.


Other **Facility/Location**



Plutonium Storage





Process?






Unattended NDA system








ID data

Date	Time	Pu mass
01/1/23	10:01	3232±12.2
01/1/23	10:02	3216±11.8
01/1/23	10:03	3178±11.1
01/1/23	10:04	3265±12.1
01/1/23	10:05	3221±12.4

Measurement Data



Remote Monitoring System



(Backup slide) Plutonium Canister Assay System

Material Type Feed PuO₂ and MOX powder


contained in storage

canister

Mass Range up to 12kg

Efficiency 13%

Measurement accuracy ~ 3%







(Backup slide)

PCAS Specification

Detector

Overall Size 60 x 147 cm (Dia. x H)

Neutron Moderator Polyethylene

Neutron Detector 24 ³He tubes

Size 2.54 x 129.5 cm (Dia. x L)

Fill Pressure 4 atm

Amplifier AMPTEC 7

Electronics Module

Shift Register JSR-12


HV Supply 1680V

LV Supply +5V

Computer Endeavor AT-700C

Printer EPSON LQ-850

Power 100V AC



PCAS#1, #4